



HEILAND VISION
GERMANY GMBH

Control unit for exposing RA4 colour paper

Order no.: LED_CTRL_COLOR

In combination with a timer, this control unit is used to expose RA4 paper.

Two filter modes are available:

- Classic subtractive filter system with settings for yellow, magenta and cyan
- Additive filter system with settings for red, green and blue

Regardless of the filter mode, the range is from zero to 400, which allows for very fine and reproducible adjustment.



A small control unit with rotary knobs and a yellow backlit LCD display allows for convenient operation on your desk. The left rotary knob has a button function for switching the focus light on and off without operating the timer.

The light source is supplied with a stabilised 24 V DC voltage. The power supply unit and an adapter for the timer are included in the scope of delivery. There are five different mains plugs (EU, US, IEC, GB or AUS) to choose from. Fig. 2 shows the EU version.



The current setting is automatically stored during power down.